

# Terysafe

Model:SS-S150

Safety Shower & Eye Washer

**Application:** Combination eye wash and safety shower. Shower is activated by pull rod and eye wash is activated by flag handle or foot treadle. Two spray type outlet heads deliver a flood of water for rinsing eyes.

**Shower Head:**10" diameter head provide water flow.

**Shower Valve:**1" IPS stainless steel valve. Valve is activated by pull rod.

**Spray Head Assembly:** Two spray heads. Each head has a dust cover, Internal flow control and filter to remove impurities from the water flow.

**Eye Wash Bowl:**11-1/2" diameter. Bowl is stainless steel.


**Eye Wash Valve:**3/8"IPS stainless steel stay-open ball valve. Valve is activated by flag handle or foot treadle. Unit remains in operation until handle is returned to closed position.

**Pipe and Fittings:** Schedule 1" and 1/2" stainless steel.

**Supply:**1-1/4" NPT female inlet.

**Waste:**1-1/4"NPT female outlet.

**Quality Assurance:**Valve,bowl and spray head assembly is factory assembled.



## Product feature

- Connect unit to uninterrupted water supply capable of delivering required flow when all components are operated simultaneously.
- Shower can provide 76 liters of water per minute.
- Center of the water pattern 16" from any obstructions.
- Large area cover of water flow, at 60", the water pattern cover 20" in diameter.
- Ball valve activates within one second.
- Easily located, accessible actuator no higher than 69".
- Controlled, low velocity flow completely rinses eyes and face is not injurious to user.
- Eye washer unit deliver 11.5 liters of water per minute.
- Outlet heads position meets 89/686/EEC and ANSI Z358.1-2004, DIN 12899 EN15154 standard.
- Protect spray heads from airborne contaminants.
- Valve actuator are easy to locate and readily accessible to user.
- Hands-free stay open valve activate within one second.
- Connect unit to uninterrupted water supply delivering at 3 GPM.